

# NWP SPARES KIT

teknek

This kit contains key components required to help you keep your clean machine fully operational.



## **Benefits to you:**

**Immediate availability of spares.**

**Maximum machine up time or availability.**

**Less risk of yield reduction.**

**Ease of fault or breakdown recovery – more self sufficiency.**

**Reduced requirement for emergency engineer visit.**

**Price reduction on buying individual parts.**

**Easy to store, kit comes in small package.**

**Easy to source, no minimum order value or endless part numbers.**



# SK52919 - 722

| Part No. | Part Name                         | Qty |
|----------|-----------------------------------|-----|
| PN48259  | Terminal Plug (male)              | 1   |
| FA49211  | Circlip, Crescent type            | 1   |
| PN32839  | Barb (M5)                         | 3   |
| PN32835  | M5 T Connector                    | 2   |
| PN48478  | Universal Elbow                   | 2   |
| HA48195  | Pyramid Bumper                    | 8   |
| SP34840  | Springs (upper) QRH               | 2   |
| SP33955  | Springs (lower) QRH               | 2   |
| ES1659   | Magnets                           | 2   |
| HA48262  | Tree plug for magnet              | 2   |
| PN32837  | Barb elbow (solenoid)             | 2   |
| SA34954  | Solenoid (upper)                  | 1   |
| SA41494  | Solenoid (lower)                  | 1   |
| PN48479  | Female Connector                  | 1   |
| PN32893  | Reducer                           | 1   |
| PN11297  | Regulator                         | 1   |
| EB41497  | Connection Board                  | 1   |
| HA35306  | Magnet Catch                      | 2   |
| EW41496  | Front Reed Switch                 | 1   |
| EW34759  | Top Rear Reed Switch              | 1   |
| MP49203  | Plastic Connect on Slide (female) | 1   |
| HA14275  | Anti-static brush (for bearing)   | 1   |
| EW48153  | LOOM - RIBBON 10 WAY SINGLE HEAD  | 1   |
| EW41498  | LOOM, CONTROL CABLE (power)       | 1   |
| EW48383  | LOOM, BTM CONTROL 520/570/622/762 | 1   |
| EW48381  | Loom Latch switch 570/622/762     | 1   |
| SP36451  | Gas Strut 762                     | 2   |

# SK52919 - 722

| <b>Part No.</b> | <b>Where Fitted</b>   |
|-----------------|---|
| <b>PN48259</b>  | <b>Brass pneumatic part outside top adhesive slide frame</b>                  |
| <b>FA49211</b>  | <b>Attached to terminal plug on outside of adhesive slide frame</b>           |
| <b>PN32839</b>  | <b>Pneumatic connection outside adhesive slide frame and top of backplate</b> |
| <b>PN32835</b>  | <b>Pneumatic connection outside adhesive slide frame and top of backplate</b> |
| <b>PN48478</b>  | <b>Pneumatic part outside adhesive slide frame</b>                            |
| <b>HA48195</b>  | <b>Rubber square at front adhesive slide frame and backplate</b>              |
| <b>SP34840</b>  | <b>Either side of upper adhesive quick release holder</b>                     |
| <b>SP33955</b>  | <b>Either side of lower adhesive quick release holder</b>                     |
| <b>ES1659</b>   | <b>Backplate and back of adhesive roll door</b>                               |
| <b>HA48262</b>  | <b>Attaches magnets and reed switches</b>                                     |
| <b>PN32837</b>  | <b>Inside top and bottom covers on solenoids</b>                              |
| <b>SA34954</b>  | <b>Pneumatic solenoid inside top cover</b>                                    |
| <b>SA41494</b>  | <b>Pneumatic solenoid inside bottom cover</b>                                 |
| <b>PN48479</b>  | <b>Pneumatic part inside top cover connected to regulator</b>                 |
| <b>PN32893</b>  | <b>Pneumatic part inside top cover connected to regulator</b>                 |
| <b>PN11297</b>  | <b>Pneumatic regulator inside top cover</b>                                   |
| <b>EB41497</b>  | <b>Main board inside top cover</b>  |
| <b>HA35306</b>  | <b>Top and bottom front plates</b>  |
| <b>EW41496</b>  | <b>Black reed switch in top and bottom front plates</b>                       |
| <b>EW34759</b>  | <b>Black reed switch in top rear plate</b>                                    |
| <b>MP49203</b>  | <b>Black plastic block attached to top head assembly frame (extrusion)</b>    |
| <b>HA14275</b>  | <b>Rubber roller block holder</b>   |
| <b>EW48153</b>  | <b>Attached to connector board in backplate</b>                               |
| <b>EW41498</b>  | <b>Attached to connector board in backplate</b>                               |
| <b>EW48383</b>  | <b>Attached to connector board in backplate (520/570/622/762)</b>             |
| <b>EW48381</b>  | <b>Switch front plate top and bottom (520/570/622/762)</b>                    |
| <b>SP36451</b>  | <b>Connected from backplate to top head assembly</b>                          |

spares kits are subject to change without notice  
in the event of changes in our supply chain.

**WORLD LEADER IN CONTACT CLEANING**

**Teknek Head Office**  
River Drive  
Inchinnan Business Park  
Renfrewshire, PA4 9RT  
Scotland, UK

T: +44 (0)141 568 8100  
F: +44 (0)141 568 8101

[www.teknek.com](http://www.teknek.com)

**Teknek Japan Ltd**  
Meiji-Yasuda Seimei Building,  
6-83 Onoe-cho, Nakaku  
Yokohama City  
Japan 231-0015

T: +81 (0)45 640 0670  
F: +81 (0)45 640 0671

**Teknek China Ltd**  
Unit G02, G/F, Myloft,  
9 Hoi Wing Road,  
Tuen Mun, N.T.,  
Hong Kong

T: +852 2468 3160  
F: +852 2462 3036

